






1 2 3 4 5 6 7 8

A-A



- NOTES
- 1 Plating (Ref. No. ③, ④)
Contact area : Gold 0.2 μ m min
Others : Gold flash
Under Plating : Nickel 2 μ m min
 - 2 The recommended clamp torque of Ref. No. ⑧ to be 1.5 to 2N·m.
Thread locker to the threaded portion of Ref. No. ① is recommended to prevent Ref. No. ⑧ from loosening. Recommended thread locker: LOCTITE 263, HENKEL JAPAN LTD.
 - 3 When this connector is mounted on to panel, be careful Ref. No. ⑥ is assembled surely into the groove of Ref. No. ① as shown in this figure to keep waterproof effectiveness.
 - 4 Rotation examples of No. ③ and ④ to ① are shown.

4	Phosphor bronze	1	8	Brass	Nickel plating
3	Copper alloy	1	7	Phosphor bronze	Nickel plating
2	PPS	(Black) UL94V-0	6	Chloroprene rubber	(Black)
1	Zinc alloy	Nickel plating	5	Phosphor bronze	Nickel plating
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 4 : 1	COUNT		DESCRIPTION OF REVISIONS
HRS		HIROSE ELECTRIC CO., LTD.	APPROVED : HY. KOBAYASHI		18.02.22
			CHECKED : HY. KOBAYASHI		18.02.22
			DESIGNED : TY. SUZUKI		18.02.22
			DRAWN : HM. SAITO		18.02.20
			DRAWING NO.		EDC-119204-31-00
			PART NO.		LF07WBRB-6SD-A(31)
			CODE NO.		CL136-1022-0-31
					1/1

FORM HC0011-5-7 1 2 3 4 5 6 7 8