




May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


HRS DRAWING FOR REFERENCE




- NOTE
- 1. ALL LEAD CO-PLANARITY SHALL BE 0.08mm MAX.
 - 2. CONTACT PLATING SPECIFICATIONS.
CONTACT AREA : GOLD 0.05 μm MIN.
SMT LEAD : GOLD 0.05 μm MIN.
UNDERPLATING : NICKEL 1 μm MIN.
(SURFACE : SEALING)
 - 3. MATA FITTING PLATING SPECIFICATIONS.
SMT LEAD : GOLD 0.05 μm MIN.
UNDERPLATING : NICKEL 1 μm MIN.
(SURFACE : SEALING)
 - 4. HRS MARK AND CAV NO. IS INDICATED IN APPROX POSITION SHOWN.

	△數	訂正事項	擔當	檢圖	年 月 日		△數	訂正事項	擔當	檢圖	年 月 日	
	COUNT	DESCRIPTION OF REVISIONS					B	Y				CHKD
△							△					
△							△					
△							△					




4	PS	CLEAR (EMBOSSED CARRIER TAPE)			
3	COOPER ALLOY	3			
2	COOPER ALLOY	2	6	PS	BLACK (PLASTIC REEL)
1	LCP	UL94 V-0, BLACK	5	POLYESTER	CLEAR (COVER TAPE)
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
REMARKS				DRAWN Y. J. LEE 17. 08. 09	DESIGNED Y. J. LEE 17. 08. 09
				CHECKED H. W. JO 17. 08. 09	APPROVED T. S. KANG 17. 08. 09
				RELEASED 17. 08. 09	
CODE NO. (OLD)		DRAWING NO. EDC3-631976		PART NO. BM23PF0.8-30DS-0.35V(895)	
	SCALE 10:1	 HIROSE KOREA CO., LTD.		CODE NO CL 6644-0048-0-895	
	UNITS mm			1/3	


6 RECOMMENDED PCB LAYOUT



RECOMMENDED METAL MASK DIMENSIONS
MATAL MASK THICKNESS : $100 \mu\text{m}$



5 RECOMMENDED REFLOW TEMPERATURE PROFILE
USING LEAD-FREE SOLDER PASTE.



REFLOW METHOD: N_2 REFLOW
NUMBER OF REFLOW CYCLES: 2 CYCLES MAX.
1) REFLOW TIME
DURATION ABOVE 220 $^{\circ}\text{C}$: 60 SEC MAX.
(PEAK TEMPERATURE: 250 $^{\circ}\text{C}$ MAX)
2) PRE-HEAT TIME
PRE-HEAT TEMPERATURE (MIN): 150 $^{\circ}\text{C}$
PRE-HEAT TEMPERATURE (MAX): 180 $^{\circ}\text{C}$
PRE-HEAT TIME: 90~120 SEC.

- 5 THIS TEMPERATURE PROFILE IS PER THE CONDITIONS SHOWN ABOVE. ADDITIONAL FACTORS, SUCH AS SOLDER PASTE TYPE, PCB SIZE AND OTHER MOUNTED COMPONENTS COULD AFFECT THE PROFILE. THEREFORE, A THOROUGH EVALUATION OF MOUNTING CONDITION IS REQUIRED PRIOR TO PRODUCTION. TEMPERATURE IS MEASURED AT CONTACT LEAD.
- 6 PLEASE CONTACT US IN CASE YOU WILL MAKE DIFFERENT SETTINGS FROM OUR RECOMMENDATION.

	DRAWING NO.	EDC3-631976	PART NO.	BM23PF0.8-30DS-0.35V(895)
	SCALE	10:1	CODE NO	CL 6644-0048-0-895
	UNITS	mm		




HRS HIROSE KOREA CO., LTD.

May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


EMBOSSED CARRIER TAPE PACKAGING (5:1)

C-C (5:1)

STYLE AND DIMENTION OF REEL (FREE)




E-E (FREE)



DETAIL OF PART No. LABEL


SUPPLIER	HIROSE ELECTRIC CO., LTD.
QUANTITY	1,000
PART NO.	BM23PF0.8-30DS-0.35V(895)
CODE NO.	CL 6644-0048-0-895
DATE OF MANUFACTURED	2024.05.01
生産月日	年 月 日
図番	** ** *
品名	BM23PF0.8-30DS-0.35V(895)
納入数量	1,000個
納入者	HIROSE KOREA

B-B (5:1)




DIRECTION OF UNREELING

D (10:1)



10 TAPING(FREE)



- 7 . PER REEL 1,000 CONNECTORS.
8 . THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.
9 REFER TO JIS C 0806, IEC-60286-3 (PACKAGING OF COMPONENTS FOR AUTOMATIC HANDLING)
10 AFTER PACKAGING. ROLL 2 METERS OF THE REINFORCEMENT COLLAR TO OUTER CIRCUMFERENCE OF TAPE AND REEL POCKET. AND TAPE DOWN AT THE END THE COLLAR.

DRAWING NO.	EDC3-631976	PART NO.	BM23PF0.8-30DS-0.35V(895)
SCALE	10:1	CODE NO.	CL 6644-0048-0-895
UNITS	mm		

HIROSE KOREA CO., LTD.

3/3