

Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

1	2	3	4																																																	
A				A																																																
B	<table border="1"><thead><tr><th>Part No.</th><th>Cable color</th></tr></thead><tbody><tr><td>~04*1TV~</td><td>WHITE</td></tr><tr><td>~04*2TV~</td><td>BLACK</td></tr></tbody></table>			Part No.	Cable color	~04*1TV~	WHITE	~04*2TV~	BLACK	B																																										
Part No.	Cable color																																																			
~04*1TV~	WHITE																																																			
~04*2TV~	BLACK																																																			
C	<p>NOTE 1 We indicate the length of the harness on the last of product name, 'L' part.</p> <p>2 Tolerance for [ L ]</p> <table border="1"><thead><tr><th>Length L [mm]</th><th>Tolerance [mm]</th></tr></thead><tbody><tr><td>35 ≤ L ≤ 200</td><td>±4</td></tr><tr><td>200 &lt; L ≤ 500</td><td>±8</td></tr><tr><td>500 &lt; L ≤ 1000</td><td>±12</td></tr><tr><td>1000 &lt; L</td><td>±1.5%</td></tr></tbody></table>			Length L [mm]	Tolerance [mm]	35 ≤ L ≤ 200	±4	200 < L ≤ 500	±8	500 < L ≤ 1000	±12	1000 < L	±1.5%	C																																						
Length L [mm]	Tolerance [mm]																																																			
35 ≤ L ≤ 200	±4																																																			
200 < L ≤ 500	±8																																																			
500 < L ≤ 1000	±12																																																			
1000 < L	±1.5%																																																			
D	<p>3. Specifications are subject to change without notice.</p>			D																																																
E	<p>【 DIMENSIONS OF CONNECTOR 】</p>			E																																																
F	<table border="1"><tr><td>1</td><td>W. FL2-LP-040HF(06)</td><td>CL331-0311-3-06</td><td>2</td><td>0.81 Dia. coaxial cable</td><td rowspan="2">HALOGEN FREE</td></tr><tr><td>NO.</td><td>PART NO.</td><td>CODE NO.</td><td>NO.</td><td>PART NO.</td></tr></table> <table border="1"><tr><td>UNITS mm</td><td></td><td>SCALE FREE</td><td>COUNT </td><td>DESCRIPTION OF REVISIONS</td><td>DESIGNED</td><td>CHECKED</td><td>DATE</td></tr></table> <table border="1"><tr><td rowspan="4"> HIROSE ELECTRIC CO., LTD.</td><td>APPROVED</td><td>TS. NOBE</td><td>18. 06. 19</td><td colspan="4">DRAWING NO.</td></tr><tr><td>CHECKED</td><td>MT. KANEKO</td><td>18. 06. 19</td><td colspan="4">PART NO. WFL2-LPHF6-04**TV-A-L 1</td></tr><tr><td>DESIGNED</td><td>MS. MATSUMOTO</td><td>18. 06. 19</td><td colspan="4">CODE NO.</td></tr><tr><td>DRAWN</td><td>MS. MATSUMOTO</td><td>18. 06. 19</td><td colspan="4"></td></tr></table>			1	W. FL2-LP-040HF(06)	CL331-0311-3-06	2	0.81 Dia. coaxial cable	HALOGEN FREE	NO.	PART NO.	CODE NO.	NO.	PART NO.	UNITS mm		SCALE FREE	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	HIROSE ELECTRIC CO., LTD.	APPROVED	TS. NOBE	18. 06. 19	DRAWING NO.				CHECKED	MT. KANEKO	18. 06. 19	PART NO. WFL2-LPHF6-04**TV-A-L 1				DESIGNED	MS. MATSUMOTO	18. 06. 19	CODE NO.				DRAWN	MS. MATSUMOTO	18. 06. 19					F
1	W. FL2-LP-040HF(06)	CL331-0311-3-06	2	0.81 Dia. coaxial cable	HALOGEN FREE																																															
NO.	PART NO.	CODE NO.	NO.	PART NO.																																																
UNITS mm		SCALE FREE	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE																																													
HIROSE ELECTRIC CO., LTD.	APPROVED	TS. NOBE	18. 06. 19	DRAWING NO.																																																
	CHECKED	MT. KANEKO	18. 06. 19	PART NO. WFL2-LPHF6-04**TV-A-L 1																																																
	DESIGNED	MS. MATSUMOTO	18. 06. 19	CODE NO.																																																
	DRAWN	MS. MATSUMOTO	18. 06. 19																																																	
FORM HC0011-5-1																																																				