



4 RECOMMENDED PATTERN




4 RECOMMENDED SOLDER PASTE: THICKNESS 100 μm

- NOTE
1. ALL LEAD CO-PLANARITY SHALL BE 0.08mm MAX.
 2. CONTACT PLATING SPECIFICATIONS.
CONTACT AREA : GOLD 0.05 μm MIN.
SMT LEAD : GOLD 0.05 μm MIN.
UNDER PLATING : NICKEL 1 μm MIN.
(SURFACE : SEALING)
 3. EACH CONTACTS 4 CORNERS ARE PROVIDED FOR METAL FITTINGS.
(NOT FOR ELECTRICAL CONNECTION)
 4. PLEASE CONTACT US IN CASE YOU WILL MAKE DIFFERENT SETTINGS FROM OUR RECOMMENDATION.


DRAWING FOR REFERENCE
This is subject to change without notice

COUNT	DESCRIPTION OF REVISIONS	B	Y	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	B	Y	CHKD	DATE
3	RE-6-0786	JSH	JHW	16. 11. 30							
2	RE-6-0807	JSH	JHW	17. 05. 23							
4	RE-6-1598	JDH	JHW	19. 10. 30							

A:A(50:1)



ENGAGEMENT FIGURE (50:1)






3	PS	CLEAR (EMBOSSED CARRIER TAPE)				5	PS	BLACK (PLASTIC REEL)			
2	COPPER ALLOY	2				4	POLYESTER	CLEAR (COVER TAPE)			
1	LCP	UL94 V-0, BLACK									
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS	REMARKS					
						DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED	
						S. H. JUNG	S. H. JUNG	H. W. JO	T. S. KANG	19.10.30	
						16.11.23	16.11.23	16.11.23	16.11.23		
						PART NO. KN13CO.7-10DP-0.4V(800)					
						CODE NO. CL 6647-0041-0-800					
						1/2					

EMBOSSED CARRIER TAPE PACKAGING (5:1)


C-C (5:1)

STYLE AND DIMENSION OF REEL (FREE)



DIRECTION OF UNREELING

B-B (5:1)




DETAIL OF PART No. LABEL

LOT NO.	*****-****
CL NO.	CL ***-****-***
PRODUCT	PART NO KN13C0.7-10DP-0.4V(800)
QUANTITY	Q'TY 8,000 PCS
SUPPLIER	HIROSE KOREA CO., Ltd.

RoHS H/F [®]	

7 TAPING(FREE)



- 5 . PER REEL 8,000 CONNECTORS.
6 . THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.
7 REFER TO JIS C 0806, IEC-60286-3 (PACKAGING OF COMPONENTS FOR AUTOMATIC HANDLING)

DRAWING NO. Δ EDC3-632681-80	PART NO. KN13C0.7-10DP-0.4V(800)
SCALE 10:1 UNITS μ	CODE NO Δ CL 6647-0041-0-800
HIROSE KOREA CO., LTD.	2/2