



Aug.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

Count	Description of revisions	By	Chkd	Date	Count	Description of revisions	By	Chkd	Date
△					△				
△					△				
Applicable standard									
Rating	Operating temperature range	-40℃ ~ +90℃			Storage temperature range	-30℃ ~ +70℃			
	Power	---W			Characteristic impedance	50Ω (0 to 8GHz)			
	Peculiarity	---			Applicable cable	-			
SPECIFICATIONS									
ITEM		TEST METHOD			REQUIREMENTS			QT	AT
CONSTRUCTION									
General examination		Visually and by measuring instrument.			According to drawing.			0	0
Marking		Confirmed visually.						0	0
ELECTRICAL CHARACTERISTICS									
Contact resistance		Mate applicable connector and apply a current of 10 mA AC(Or 10,000Hz).			Center contact : 30 mΩ Max. Outer contact : 30 mΩ Max.			0	-
Insulation resistance		Mate applicable connector and apply a voltage of DC 100 V.			500 MΩ Min.			0	-
Voltage proof		Mate applicable and apply a voltage of AC 200 V for 1 min.			No flashover or breakdown.			0	-
Voltage standing wave ratio (Note 2)		Frequency 0 to 8GHz.			VSWR 1.6 Max.			0	-
MECHANICAL CHARACTERISTICS									
Mechanical operation		30 times insertions and extractions.			① Contact resistance Center contact : 50 mΩ Max. Outer contact : 50 mΩ Max. ② No damage, crack and looseness of parts.			0	-
Shock		980 m/s ² direction of pulse 6ms at 10 times in 3 directions.			① No electrical discontinuity of 1μs. ② Contact resistance Center contact : 50 mΩ Max. Outer contact : 50 mΩ Max. ③ No damage, crack and looseness of parts.			0	-
ENVIRONMENTAL CHARACTERISTICS									
Rapid change of temperature (NOTE 1)		Temperature : -40±2 → 15~35 → +90±2 → 15~35 ℃ Time : 30 → 5 → 30 → 5 min Under 200 cycles.			① Contact resistance Center contact : 50 mΩ Max. Outer contact : 50 mΩ Max.			0	-
Damp heat, cycle (NOTE 1)		Exposed at 25±2 ℃, 65 % 25 h.  Under 10 cycles.			② No damage, crack or looseness of parts. ③ Insulation resistance : 10 MΩ Min.			0	-
Remarks conditions for testing				Drawn	Designed	Checked	Approved	Released	
				H.G PARK	H.G PARK	D.G KIM	H.S KIM		
Unless otherwise specified, refer to JIS C 5402.				19.03.06	19.03.06	19.03.06	19.03.06		
Note QT: Qualification test AT: Assurance test O: Applicable test									
HIROSE KOREA CO.,LTD.				SPECIFICATION SHEET			Part No.		
							U.FL-R-SMT-K(800)		
Code No.(OLD)		Drawing No.		Code No.				1/2	
CL		ELC4-632635		CL 6327-0362-5-800					


Dry heat (NOTE 1)	Exposed at 90±2 °C, 300 h.	① Contact resistance Center contact : 50 mΩ Max. Outer contact : 50 mΩ Max. ② No damage, crack or looseness of parts. ③ Insulation resistance : 10 MΩ Min.	O	-
Damp and humidity heat (NOTE 1)	Exposed at 90±2 °C, 85%, 500 h.	① Contact resistance Center contact : 50 mΩ Max. Outer contact : 50 mΩ Max. ② No damage, crack or looseness of parts. ③ No evidence of corrosion which affects to operation of connector. ④ Insulation resistance : 10 MΩ Min.	O	-
Corrosion salt spray (NOTE 1)	Exposed at 35±2 °C, 5±1 % salt water spray for 48 h.	① Contact resistance Center contact : 50 mΩ Max. Outer contact : 50 mΩ Max. ② No damage, crack or looseness of parts. ③ No evidence of corrosion which affects to operation of connector.	O	-
Sulfur dioxide test (NOTE 1)	Exposed in 10 PPM, 40±2 °C, 90~95 % FOR 24 h.	① Contact resistance Center contact : 50 mΩ Max. Outer contact : 50 mΩ Max. ② No damage, crack or looseness of parts. ③ Insulation resistance : 10 MΩ Min.	O	-
Dust resistance (NOTE 1)	1) Kind of dust : JIS R5210 cement of portland, 1.5 Kg. 2) 10 seconds every 15 minutes, 1h progressing.	① Contact resistance Center contact : 50 mΩ Max. Outer contact : 50 mΩ Max. ② No damage, crack or looseness of parts. ③ Insulation resistance : 10 MΩ Min.	O	-
Resistance to soldering heat	Reflow soldering : Peak temp : 260 °C Max for 30 s Min. Reflow temp : 180 °C for 60~120 s. 3 cycle.	① No deformation of case of excessive looseness of the terminals. ② No damage of electrical performance coating of solder.	O	-

COMBINE VIBRATION CHARACTERISTICS

Combine vibration test (NOTE 1)	Exposed at 85±2°C, 90~95 %, 120 cycles (45 min : 0n, 15 min : Off) Vibration acceleration 4.4 g (43.12 m/s ²). Frequency 20 ~ 200 Hz at 40 h, in 3 directions.	① No electrical discontinuity of 1 μs. ② Contact resistance Center contact : 50 mΩ Max. Outer contact : 50 mΩ Max. ③ No damage, crack and looseness of parts.	O	-
------------------------------------	--	---	---	---

(NOTE 1) 10 times insertions and extractions the pre-test / exposed 24h.
Exposed 2h after the test.

(Note 2) Test item [VSWR] and conducted according to the conditions specified below.



Note QT: Qualification test AT: Assurance test O: Applicable test

HIROSE KOREA CO.,LTD.		SPECIFICATION SHEET		Part No. U.FL-R-SMT-K(800)	
Code No.(OLD) CL	Drawing No. ELC4-632635	Code No. CL 6327-0362-5-800	2/2		