

Apr.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-55℃ TO +85℃(note1)		STORAGE TEMPERATURE RANGE	-10℃ TO +60℃
	VOLTAGE	50 V AC/DC		APPLICABLE CONNECTOR	BK13H-60DP/2-0.35V**(**)
	CURRENT	SIGNAL CONTACT 0.2A(note2) POWER CONTACT 5.0A			

### SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
------	-------------	--------------	----	----

CONSTRUCTION				
GENERAL EXAMINATION	CONFIRMED VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING	CONFIRMED VISUALLY.		X	X

ELECTRICAL CHARACTERISTICS				
CONTACT RESISTANCE	20mV AC OR LESS 1kHz, 1mA	SIGNAL CONTACT : 50mΩ MAX POWER CONTACT : 15mΩ MAX	X	-
INSULATION RESISTANCE	100V DC	50MΩ MIN	X	-
VOLTAGE PROOF	150V AC FOR 1min.	NO FLASHOVER OR BREAKDOWN	X	-

MECHANICAL CHARACTERISTICS				
MECHANICAL OPERATION	30 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: SIGNAL CONTACT : 50mΩ MAX POWER CONTACT : 15mΩ MAX ② NO DAMAGE, CRACK OR LOOSENESS OF PATRS.	X	-
VIBRATION	FREQUENCY 10 TO 55 TO 10 Hz, APPROX 5min SINGLE AMPLITUDE 0.75mm, 10CYCLES, FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
SHOCK	490 m/s² DURATION OF PULSE 11ms AT 3 TIMES FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-

ENVIRONMENTAL CHARACTERISTICS				
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55 → +85℃ TIME 30 → 30 min UNDER 5 CYCLES. (RELOCATION TIME TO CHAMBER: WITHIN2~3 MIN)	① CONTACT RESISTANCE: SIGNAL CONTACT : 50mΩ MAX POWER CONTACT : 15mΩ MAX ② INSULATION RESISTANCE: 50MΩ MIN ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
DAMP HEAT (STEADY STATE)	EXPOSED AT 40±2℃, 90 TO 95%, 96h.	① CONTACT RESISTANCE: SIGNAL CONTACT : 50mΩ MAX POWER CONTACT : 15mΩ MAX ② INSULATION RESISTANCE: 25MΩ MIN ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
SULPHUR DIOXIDE	EXPOSED IN 25 PPM FOR 96h, 25℃, 75±5%RH. (Test standard : JIS C 60068)	① CONTACT RESISTANCE: SIGNAL CONTACT : 50mΩ MAX POWER CONTACT : 15mΩ MAX ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-

## REFERENCE DRAWING

REMARKS Note 1 : INCLUDE THE TEMPERATURE RISING BY CURRENT. Note 2 : MAX 8A AT TOTAL PIN CONTACTS. Unless otherwise specified, refer to JIS C 5402 and IEC 60512	DRAWN S.W.JUNG 25.02.28	DESIGNED S.W.JUNG 25.02.28	CHECKED S.H.PARK 25.02.28	APPROVED H.W.JO 25.02.28	RELEASED ENG 25.02.28 DEPT
---	-------------------------------	----------------------------------	---------------------------------	--------------------------------	-------------------------------------

HIROSE KOREA CO.,LTD.	SPECIFICATION SHEET	PART NO. BK13H-60DS/2-0.35V10(895)
CODE NO.(OLD) CL	DRAWING NO. ELC4-633784-95	CODE NO. CL 6671-0020-4-895