



A-A (Wire barrel cross-section image)



B-B (Insulation barrel cross-section image)



Check point		Measure (mm)	
Cover location.	C	0.2~0.7	
Location of tip of the core.	D	0.2~0.5	
Bell-mouth.	E1	0.1~0.3	
	E2	2	
	E3	1.7 MAX	
Bent-up.	F	4°MAX	
Bent-down.	G	3°MAX	
Twist.	H	±2°MAX	
Rolling.	I	±5°MAX	
Cut-off tab.	J	0.1MAX	
Strip length prior to crimping.	K	3 1.7~2.3	
Height of metal cut-out teeth.	L	0.1MAX	
Width.	Wire barrel.	M	1.7MAX
	Insulation barrel.	N	1.7MAX
Difference in level on transition part	P	0.2MAX	
Gap dimension	Q	0.14~0.22	

Note 1 To adjust applicator, please check the crimping condition (crimping height and configuration) by using cable.

① ② DF62W-2830SC(F)(A) . . . 0.1~0.3

DF62W-2226SC(F)(A) . . . 0.1~0.3

DF62W-2022SC(F)(A) . . . AWG20 : 0.2 ~ 0.4 , AWG22 : 0.15~0.4

③ This dimension is for reference. please adjust it to meet specified dimensions after the crimping.

COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE												
① 1	DIS-H-00006054	HT. SATO	HS. OKAWA	20200618												
TITLE		<div style="display: flex; align-items: center;"> HIROSE ELECTRIC CO., LTD. </div> <table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td>APPROVED</td> <td>HS. OKAWA</td> <td>20181003</td> </tr> <tr> <td>CHECKED</td> <td>SZ. ONO</td> <td>20181003</td> </tr> <tr> <td>CHARGED</td> <td>HT. SATO</td> <td>20181003</td> </tr> <tr> <td>WRITTEN</td> <td>SK. CHIBA</td> <td>20181002</td> </tr> </table>			APPROVED	HS. OKAWA	20181003	CHECKED	SZ. ONO	20181003	CHARGED	HT. SATO	20181003	WRITTEN	SK. CHIBA	20181002
APPROVED	HS. OKAWA				20181003											
CHECKED	SZ. ONO				20181003											
CHARGED	HT. SATO				20181003											
WRITTEN	SK. CHIBA	20181002														
DF62W-**SC**																
Crimping Quality Standard																
TECHNICAL SPECIFICATION		ETAD-H0763-00	①	1/1												