





Dec.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

△ RECOMMENDED LAND PATTERN DIMENSION OF PCB



△ RECOMMENDED METAL MASK  
Aperture ratio 100% : t=0.15


- Note
- 1 Lead CO-Planarity is 0.1mm MAX.
  - 2 Floating range of this connector is ±0.7mm MAX.  
The maximum cycle time of the floating operation is in accordance with the mating cycle of the connector.
  - 3 Please use the connectors within the specified PCB distance.  
Please refer to the drawings of mating connector.
  - 4 Blemish and hit mark can be occurred through out the manufacturing process which doesn't affect quality level.
  - 5 The dimensions in parentheses are for references.
  - 6 This is packaged in embossed carrier tape. (200pcs/RL)
  - 7 It shows the vacuum pickup area. Remove the pickup cap before mating connectors.
  - 8 This connector has no polarity with the mating connector.
  - △ 9 Arrangement of via-hole is prohibited in area.
  - △ 10 Arrangement of pattern and via-hole are prohibited in area.

|   |                 |   |
|---|-----------------|---|
| 7 | POLYAMIDE       | ( CAP FOR VACUUM PICKUP)  |
| 6 | POLYESTER       | ( EMBOSSED COVER TAPE)  |
| 5 | POLYSTYRENE     | ( EMBOSSED CARRIER TAPE)  |
| 4 | PHOSPHOR BRONZE | OVER PLATING : TIN-PLATING 1 μm<br>UNDER PLATING : NICKEL 0.5 μm                      |
| 3 | COPPER ALLOY    | CONTACT AREA : GOLD 0.1 μm<br>LEAD AREA : GOLD 0.03 μm<br>UNDER PLATING : NICKEL 1 μm |



|                       |           |               |       |             |          |                          |          |              |          |             |      |          |
|-----------------------|-----------|---------------|-------|-------------|----------|--------------------------|----------|--------------|----------|-------------|------|----------|
| 1, 2                  | POLYAMIDE | BLACK UL94V-0 | NO.   | MATERIAL    | FINISH . | REMARKS                  | NO.      | MATERIAL     | FINISH . | REMARKS     |      |          |
| UNITS                 | mm        | SCALE         | 2 : 1 | COUNT       | 2        | DESCRIPTION OF REVISIONS | DESIGNED | KI. YAMAZAKI | CHECKED  | KN. SHIBUYA | DATE | 20200831 |
| APPROVED : HH. SHINDO |           | 20190719      |       | DRAWING NO. |          | EDC-387245-00-00         |          |              |          |             |      |          |
| CHECKED : KN. SHIBUYA |           | 20190718      |       | PART NO.    |          | FX26-60P-1SV5            |          |              |          |             |      |          |
| DESIGNED : TK. ABE    |           | 20190718      |       | CODE NO.    |          | CL576-1506-0-00          |          |              |          |             |      |          |
| DRAWN : TK. ABE       |           | 20190718      |       |             |          |                          |          |              |          |             |      |          |

Dec.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

6 DRAWING FOR PACKING(2:1)



REEL DIMENSION(No scale)



|            |             |                  |     |
|------------|-------------|------------------|-----|
| <b>HRS</b> | DRAWING NO. | EDC-387245-00-00 | 4/2 |
|            | PART NO.    | FX26-60P-1SV5    |     |
|            | CODE NO.    | CL576-1506-0-00  |     |
|            |             |                  |     |