





Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



NOTES

- LEAD CO-PLANARITY SHALL BE 0.1mm MAX.
- STIFFENER IS REQUIRED FOR MOUNTING ONTO FPC IN ORDER TO AVOID STRESS BY FPC SLACKING TO MOUNTED CONNECTOR.
- LOT No. INFORMATION IS SHOWN IN THE TABLE.
EXAMPLE:8GFD
-YEAR:2008 MONTH:July DAY:15 LINE No.:4
- UNMATING SHALL BE DONE WITH THE SPECIFIC EXTRACTION TOOL.
- SOLDERING REWORK IS NOT POSSIBLE SINCE SOLDERING LEADS ARE COVERED BY METAL SHIELDING.


| YEAR | MONTH | DAY | | | | | | LINE No. | | | |
|------|-------|-------|------|-----|------|-----|------|----------|------|----------|------|
| YEAR | CODE | MONTH | CODE | DAY | CODE | DAY | CODE | DAY | CODE | LINE No. | CODE |
| 10 | 0 | Jan | A | 1 | 1 | 11 | B | 21 | M | 1 | A |
| 11 | 1 | Feb | B | 2 | 2 | 12 | C | 22 | N | 2 | B |
| 12 | 2 | Mar | C | 3 | 3 | 13 | D | 23 | P | 3 | C |
| 13 | 3 | Apr | D | 4 | 4 | 14 | E | 24 | Q | 4 | D |
| 14 | 4 | May | E | 5 | 5 | 15 | F | 25 | R | 5 | E |
| 15 | 5 | Jun | F | 6 | 6 | 16 | G | 26 | S | 6 | F |
| 16 | 6 | Jul | G | 7 | 7 | 17 | H | 27 | T | 7 | G |
| 17 | 7 | Aug | H | 8 | 8 | 18 | J | 28 | U | 8 | H |
| 08 | 8 | Sep | I | 9 | 9 | 19 | K | 29 | V | 9 | I |
| 09 | 9 | Oct | J | 10 | A | 20 | L | 30 | W | 10 | J |
| | | Nov | K | | | | | 31 | X | | |
| | | Dec | L | | | | | | | | |

| NO. | MATERIAL | FINISH | REMARKS | NO. | MATERIAL | FINISH | REMARKS |
|-----|-----------------|--------|---|-----|-----------------|--------|---|
| 2 | LCP | | UL94V-0 | 6 | PS | | BLACK |
| | | | | 5 | POLYESTER | | CLEAR |
| 1 | PHOSPHOR BRONZE | | CONTACT AREA : Au PLATING 0.3µm min LEAD AREA : Au PLATING 0.1µm min UNDER PLATING : Ni PLATING 2µm min | 4 | PS | | CLEAR |
| | | | | 3 | PHOSPHOR BRONZE | | WHOLE AREA : Sn PLATING 1µm min UNDER PLATING : Cu PLATING 0.2µm min |

| UNITS | SCALE | COUNT | DESCRIPTION OF REVISIONS | DESIGNED | CHECKED | DATE |
|-------|-------|-------|--------------------------|-----------|-----------|----------|
| mm | 5 : 1 | 4 | DIS-H-003408 | SI. ISHII | MN. KENJO | 08.10.30 |

| APPROVED | DATE | DRAWING NO. | PART NO. | CODE NO. |
|------------|----------|--------------------|----------|----------|
| TY. OMA | 07.01.11 | EDC3-310170-01 | | |
| TS. SAKATA | 07.01.11 | DF36A-40S-0.4V(51) | | |
| MN. KENJO | 07.01.09 | CL662-4003-6-51 | | |
| MN. KENJO | 07.01.09 | | | |

Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



| | | |
|------------|-------------|--------------------|
| HRS | DRAWING NO. | EDC3-310170-01 |
| | PART NO. | DF36A-40S-0.4V(51) |
| | CODE NO. | CL662-4003-6-51 |
| | | \triangle 2/2 |