








RECOMMENDED CABLE SUBASSEMBLY



A-A (FREE)



CABLE TERMINATION FIGURE(FREE)



- NOTES 1. APPLICABLE CABLE: THIN COAXIAL CABLE (AWG#42-AWG#46)
2. THIS CONNECTOR IS NOT HOT PLUGGABLE. MATE AND UNMATE WHILE THE POWER IS OFF.
3. THE ASSEMBLY IS COMPLETED BY COMBINING TWO PARTS "CONNECTOR UNIT AND METAL SHIELDING".
REFER TO THE TABLE FOR EACH ITEM No., PART NAME, PART No. AND CODE No.

ITEM No.	PART NAME	PART No.	CODE No.
1, 2	CONNECTOR UNIT	DF36-30P-0.4SD(51)	CL662-4018-3-51
-	METAL SHIELDING	DF36A-30P-SHL	CL662-4019-6-00

1	PHOSPHOR BRONZE	CONTACT AREA : Au PLATING 0.1µm min TERMINATION AREA : Au PLATING 0.1µm min UNDER PLATING : Ni PLATING 1µm min	5	PS	BLACK
NO.	MATERIAL	FINISH, REMARKS	4	POLYESTER	CLEAR
UNITS	mm	SCALE	3	PS	CLEAR
mm	5 : 1	COUNT	2	LCP	UL94V-0, BLACK
DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE		
APPROVED : TS. SAKATA	11.10.18	DRAWING NO.	EDC3-315347-01		
CHECKED : IO. DENPOUYA	11.10.18	PART NO.	DF36-30P-0.4SD(51)		
DESIGNED : TP. MATSUMOTO	11.10.17	CODE NO.	CL662-4018-3-51		
DRAWN : TP. MATSUMOTO	11.10.17				

