APPLICA	BLE STAN	DARD									
OPERATING TEMPERATUR		E RANGE	-55 °C TO 10	5 °C		STORAGE TEMPERATURE R		-10	-10°CTO 50°C (PACKED CONDITIO		
RATING	VOLTAGE CURRENT		50 V AC / DC		_	ATING C	R STORAGE E	RELA	пуениміріту 90 % мах	(NOT D	EWED
			0.5 A		APPL	ICABLE	CABLE	t=0	0.3±0.03mm, GOLD	PLAT	NG
		l	SPEC	IFIC	ATIO	NS			·		
IT	EM		TEST METHOD				REC	QUIRE	MENTS	QT	АТ
CONSTR	UCTION	•									
	XAMINATION		Y AND BY MEASURING IN	ISTRUM	IENT.	ACCO	ACCORDING TO DRAWING.				×
MARKING			MED VISUALLY.							×	×
VOLTAGE P		RACTERISTICS				NO ELACHOVED OD DDEAKDOWN				1	
INSULATION		250 V AC FOR 1 min. 100 V DC.					NO FLASHOVER OR BREAKDOWN. 500 MΩ MIN.			×	×
RESISTANC	E					300 1015	2 IVIIIN.			×	_ ×
CONTACT F	RESISTANCE	AC/DC 20 mV MAX (AC:1 KHz) , 1 mA .				100 mg	2 MAX.			×	×
							INCLUDING FPC,FFC BULK RESISTANCE (L=8mm)				
MECHAN	IICAL CHA	RACTE	RISTICS			1 -					
VIBRATION		FREQUENCY 10 TO 55 Hz, HALF AMPLITUDE				0	① NO ELECTRICAL DISCONTINUITY OF				_
SHOCK		0.75 mm, FOR 10 CYCLES IN 3 AXIAL DIRECTIONS. 981 m/s ² , DURATION OF PULSE 6 ms					1 μs. ② CONTACT RESISTANCE: 100 mΩ MAX.				+_
		AT 3 TIMES IN 3 BOTH AXIAL DIRECTIONS.				③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.					
MECHANICA OPERATION		20 TIMES INSERTIONS AND EXTRACTIONS.				① CONTACT RESISTANCE: $100 \text{ m}\Omega$ MAX. ② NO DAMAGE, CRACK AND LOOSENESS					-
FPC RETEN	TION FORCE	MEASURED BY APPLICABLE FPC. (THICKNESS OF FPC SHALL BE t=0.30mm AT INITIAL CONDITION.)					OF PARTS. DIRECTION OF INSERTION:			×	+_
						(TOF	CONTACT	Γ)			
						l l	X NUMBER TOM CON		ONTACTS MIN.		
									ONTACTS MIN.		
ENN/IDOI	INACNITAL		OTEDIOTION			(not	e 1)				
			CTERISTICS	T \\/ \ \ T E	D	① CO	NITACT DE	CICTA	NCE: 100 mΩ MAX	×	
		EXPOSED AT 35±2 °C , 5 % SALT WATER SPRAY FOR 96 h.				NO DAMAGE, CRACK AND LOOSENESS OF PARTS. NO EVIDENCE OF CORROSION WHICH					
						AFFECTS TO OPERATION OF CONNECTOR.					
RAPID CHANGE OF TEMPERATURE		TEMPERATURE-55→+15T0+35→ +105→+15T0+35°C /2			(1) CONTACT RESISTANCE: $100 \text{ m}\Omega$ MAX. (2) INSULATION RESISTANCE: $50 \text{ M}\Omega$ MIN. (3) NO DAMAGE, CRACK AND LOOSENESS				×	-	
		TIME $30 \rightarrow 2 \text{ To } 3 \rightarrow 30 \rightarrow 2 \text{ To } 3 \text{ min}$									
	-	UNDER 5 CYCLES.				OF	OF PARTS.				
DAMP HEAT (STEADY S		EXPOSED AT 40±2 °C, RELATIVE HUMIDITY 90 TO 95 %, 96 h.							×	-	
DAMP HEAT, CYCLIC		EXPOSED AT -10 TO +65 °C,			_	① CONTACT RESISTANCE: $100 \text{ m}\Omega$ MAX.				1-	
		RELATIVE HUMIDITY 90 TO 96 %, 10 CYCLES,TOTAL 240 h.			② INSULATION RESISTANCE: 1 M Ω MIN. (AT HIGH HUMIDITY)						
						3 INS	③ INSULATION RESISTANCE: 50 MΩ MIN.				
						(AT DRY) ① NO DAMAGE, CRACK AND LOOSENESS OF PARTS.					
COUN	T DE	SCRIPTIC	ON OF REVISIONS		DESIG	l	. ,		CHECKED	D/	ATE
3		DIS-F	F-00005614		SE. YOK	OYAMA			HS. HIRAHARA	202	00611
REMARK					APPROVED CHECKED		D	MO. ISHIDA		20131129	
This product is RoHS compliant.			nt				-	HS. SAKAMOTO		20131129	
·						DESIGNED		-			31128
Unless otherwise specified, refer to IEC 60512.				DRAWN NM. SANPEI			20131128				
					RAWING NO.		1216	ELC4-159714-04 34SRJ-*S-0. 5SH (50)			
KS	SPECIFICATION SHEET HIROSE ELECTRIC CO., LTD.			PART				(0) (A	1/2		
	-2-1	COL LELOTINO CO., LTD. COL			CODE	: NO. GL300			<u> </u>	1/2	

SPECIFICATIONS							
ITEM	TEST METHOD .	REQUIREMENTS	QT	АТ			
DRY HEAT	EXPOSED AT 105±2 °C, 96 h. 2	① CONTACT RESISTANCE: 100 mΩ MAX.	×	_			
COLD	EXPOSED AT -55±3°C, 96 h.	② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	_			
[JIS C 60068-2-42]	EXPOSED AT 40±2 °C , RELATIVE HUMIDITY 80±5% 25±5 ppm FOR 96 h.	 CONTACT RESISTANCE: 100 mΩ MAX. NO DAMAGE, CRACK AND LOOSENESS OF PARTS. 	×	_			
	EXPOSED AT 40±2 °C , RELATIVE HUMIDITY 80±5% , 10 TO 15 ppm FOR 96 h.	③ NO EVIDENCE OF CORROSION WHICH AFFECTS TO OPERATION OF CONNECTOR.	×	_			
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, 235±5°C FOR IMMERSION DURATION, 2±0.5 sec.	A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.	×	_			
RESISTANCE TO SOLDERING HEAT	1) REFLOW SOLDERING: PEAK TMP. 250 °C MAX. REFLOW TMP. OVER 230 °C WITHIN 60 sec. 2) SOLDERING IRONS: TMP. 350 ± 10 °C FOR 5±1 sec.	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	×	_			

(note1)

FASTEN FPC ON PCB OR SOMETHING FIXED IF FORCE IN VERTICAL DIRECTION SHALL BE PREDICTED. DO NOT CLOSE THE ACTUATOR BEFORE INSERTING FPC EVEN AFTER THE CONNECTOR IS MOUNTED ONTO A PCB. CLOSING THE ACTUATOR WITHOUT FPC COULD MAKE THE CONTACT GAP SMALLER, WHICH INCREASES THE FPC INSERTION FORCE.

THIS CONNECTOR HAS CONTACTS ON THE BOTH TOP AND BOTTOM.

THERE'S A CASE WHICH FPC/FFC RETENTION FORCE DOESN'T FULFILL THE VALUE, BECAUSE FPC SPECIFICATION AFFECTS THE RESULT OF FPC/FFC RETENTION FORCE.

Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWIN	NG NO.	ELC4-159714-04		
Н	RS	SPECIFICATION SHEET	PART NO.	FH34SRJ-*S-0. 5SH (50)			
• •	. •	HIROSE ELECTRIC CO., LTD.	CODE NO		CL580	A	2/2