

Jun.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

Applicable standard				
Rating	Operating Temperature Range	-55 to +85°C (Note1)	Storage Temperature Range	-10 °C to +60°C (Note3)
	Operating Humidity Range	20% to 80% (Note2)	Storage Humidity Range	40% to 70% (Note3)
	Voltage	50 V AC/DC	Applicable Connector	DF53-16P-0.6C(##)
	Current	All pin	AWG 32 : 0.7A	
Any of 2 pins as a power		AWG 32 : 1.3A(power), 0.5A(signal)		

Specifications

Item	Test method	Requirements	QT	AT
Construction				
General Examination	Visually and by measuring instrument.	According to drawing.	X	X
Marking	Confirmed visually.		X	X
Electric Characteristics				
Contact Resistance	20mV MAX, 1mA (DC or 1000Hz).	20 mΩ MAX.	X	—
Insulation Resistance	100 V DC.	100 MΩ MIN.	X	—
Voltage Proof	200 V AC for 1 min.	No flashover or breakdown.	X	—
Mechanical Characteristics				
Mechanical Operation	20 times insertion and extraction.	1.Contact resistance: 40 mΩ MAX. 2.No damage, crack or looseness of parts.	X	—
Mating and unmating force	It takes out and inserts with a conformity connector.	1.Mating Force : 22.4N MAX. 2.Unmating Force : 4.6N MIN.	X	—
Vibration	Frequency 10 to 55 Hz, single amplitude 0.75 mm, at 10 cycles for 3 direction.	1.No electrical discontinuity of 1 μ s. 2.No damage, crack or looseness of parts.	X	—
Shock	Acceleration 500 m/s ² duration of pulse 11 ms at 3 times for 3 directions.		X	—
Environmental Characteristics				
Damp Heat (Steady State)	Exposed at 40 ± 2°C , humidity 90 to 95 %, 96 h. (After leaving the room temperature for 1 to 2h.)	1.Contact resistance: 40 mΩ MAX. 2.Insulation resistance: 100 MΩ MIN. 3.No damage, crack or looseness of parts.	X	—
Rapid Change Of Temperature	Temperature -55°C→ +85°C Time 30min→ 30min Under 5 Cycles. (The transferring time of the tank is 2 to 3 MIN) (After leaving the room temperature for 1 to 2h.)	1.Contact resistance: 40 mΩ MAX. 2.Insulation resistance: 100 MΩ MIN. 3.No damage, crack or looseness of parts.	X	—
Dry Heat	Exposed at 85±2°C, 96h	1.Contact resistance: 40 mΩ MAX. 2.Insulation resistance: 100 MΩ MIN. 3.No damage, crack or looseness of parts.	X	—
Cold	Exposed at -55±3°C, 96h	1.Contact resistance: 40 mΩ MAX. 2.Insulation resistance: 100 MΩ MIN. 3.No damage, crack or looseness of parts.	X	—

Remarks
 Note 1: Include the temperature rising by current.
 Note 2: No condensing
 Note 3: Applicable to unused product packaging.

COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
0				

Unless otherwise specified, refer to IEC 60512.	APPROVED	SJ. OKAMURA	20230829
	CHECKED	SZ. ONO	20230829
	DESIGNED	JN. TONAI	20230829
	DRAWN	JN. TONAI	20230829

Note QT:Qualification Test AT:Assurance Test X:Applicable Test DRAWING NO. ELC-380628-00-00

HRS	SPECIFICATION SHEET	PART NO.	DF53-16S-0.6H	
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL0668-1010-0-00	△ 1/2

Jun.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

Specifications					
Item	Test method	Requirements	QT	AT	
Resistance to soldering heat	<< Reflow area >> Number of cycles : 2 cycles MAX 250°C MAX 10 sec MAX 220°C MIN 60 sec MAX << Preheating area >> 150°C to 180°C 90 sec to 120 sec	No deformation of case of excessive looseness of the terminals.	X	—	
Solderability	Soldered at solder temperature, 245°C for insertion duration, 5sec.	Solder shall cover a minimum of 95 % of the surface being immersed.	X	—	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.		ELC-380628-00-00	
	SPECIFICATION SHEET		PART NO.	DF53-16S-0. 6H	
	HIROSE ELECTRIC CO., LTD.		CODE NO	CL0668-1010-0-00	△