

APPLICABLE STANDARD						
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO 125 °C	STORAGE TEMPERATURE RANGE	-10 °C TO 50 °C (PACKED CONDITION)		
	VOLTAGE	50 V AC / DC	OPERATING OR STORAGE HUMIDITY RANGE	RELATIVE HUMIDITY 90 % MAX (NOT DEWED)		
	CURRENT	0.5 A	APPLICABLE CABLE	t=0.3±0.05mm, GOLD PLATING HEAT RESISTANCE : 125°C		
SPECIFICATIONS						
ITEM		TEST METHOD		REQUIREMENTS		
CONSTRUCTION						
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	×	
MARKING		CONFIRMED VISUALLY.			×	
ELECTRICAL CHARACTERISTICS						
CONTACT RESISTANCE		1mA(DC OR 1000Hz).		50 mΩ MAX. INCLUDING FPC,FPC BULK RESISTANCE (L=8mm)	×	
INSULATION RESISTANCE		100 V DC.		500 MΩ MIN.	×	
VOLTAGE PROOF		150 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	×	
MECHANICAL CHARACTERISTICS						
MECHANICAL OPERATION		20 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 50 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	
VIBRATION		FREQUENCY 10 TO 55 Hz, HALF AMPLITUDE 0.75 mm, FOR 10 CYCLES IN 3 AXIAL DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② CONTACT RESISTANCE: 50 mΩ MAX.	×	
SHOCK		981 m/s ² , DURATION OF PULSE 6 ms AT 3 TIMES IN 3 BOTH AXIAL DIRECTIONS.		③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	
FPC RETENTION FORCE		MEASURED BY APPLICABLE FPC. (CONNECTOR,FPC AT INITIAL CONDITION. THICKNESS OF FPC SHALL BE t=0.30mm)		DIRECTION OF INSERTION: 0.4×n N MIN (n : NUMBER OF CONTACTS). (note 1)	×	
ENVIRONMENTAL CHARACTERISTICS						
RAPID CHANGE OF TEMPERATURE		TEMPERATURE-55→+15T ₀ +35→+125→+15T ₀ +35°C TIME 30→ 2 TO 3 → 30→ 2 TO 3 min. UNDER 1000 CYCLES.		① CONTACT RESISTANCE: 50 mΩ MAX. ② INSULATION RESISTANCE: 50 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	
DAMP HEAT (STEADY STATE)		EXPOSED AT 60±2 °C, RELATIVE HUMIDITY 90 TO 95 %, 1000 h.			×	
DAMP HEAT,CYCLIC		EXPOSED AT -10 TO +65 °C, RELATIVE HUMIDITY 90 TO 96 %, 10 CYCLES,TOTAL 240 h.		① CONTACT RESISTANCE: 50 mΩ MAX. ② INSULATION RESISTANCE: 1 MΩ MIN. (AT HIGH HUMIDITY) ③ INSULATION RESISTANCE: 50 MΩ MIN. (AT DRY) ④ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	
DRY HEAT		EXPOSED AT 125±2 °C, 1000 h.		① CONTACT RESISTANCE: 50 mΩ MAX.	×	
COLD		EXPOSED AT -55±3°C, 1000 h.		② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	
CORROSION SALT MIST		EXPOSED AT 35±2 °C 5% SALT WATER SPRAY FOR 96 h.		① CONTACT RESISTANCE: 50 mΩ MAX. ② NO EVIDENCE OF CORROSION WHICH AFFECTS TO OPERATION OF CONNECTOR.	×	
SULPHUR DIOXIDE [JIS C 60068-2-42]		EXPOSED AT 40±2 °C , RELATIVE HUMIDITY 80±5% , 25±5 ppm FOR 96 h.			×	
HYDROGEN SULPHIDE [JIS C 60068-2-43]		EXPOSED AT 40±2 °C , RELATIVE HUMIDITY 80±5% , 10 TO 15 ppm FOR 96 h.			×	
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
△						
REMARK			APPROVED	HS. SAKAMOTO	20191025	
			CHECKED	FN. TAMURA	20191025	
			DESIGNED	TA. SUZUKI	20191025	
			DRAWN	TA. SUZUKI	20191025	
Unless otherwise specified, refer to IEC 60512.						
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.	ELC-386059-05-00		
	SPECIFICATION SHEET		PART NO.	FH52K-80S-0. 5SH (05)		
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL580-4641-0-05	△ 1/2	

SPECIFICATIONS					
ITEM	TEST METHOD	REQUIREMENTS	QT	AT	
RESISTANCE TO SOLDERING HEAT	1) REFLOW SOLDERING (TO BE 2 TIMES MAX.) PEAK TMP. 250 °C MAX REFLOW TMP. OVER 230 °C WITHIN 60 sec. PRE-HEATING. 150 TO 200°C 90 TO 120 sec. 2)SOLDERING IRONS : 400 ± 10 °C, FOR 5± 1 sec .	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	X	—	
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, 245±3 °C FOR IMMERSION DURATION, 3±0.3 sec.	A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.	X	—	
(note 1) THERE'S A CASE WHICH FPC/FFC RETENTION FORCE DOESN'T FULFILL THE VALUE, BECAUSE FPC/FFC SPECIFICATION AFFECTS THE RESULT OF FPC/FFC RETENTION FORCE.					
Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.		ELC-386059-05-00	
	SPECIFICATION SHEET	PART NO.	FH52K-80S-0. 5SH (05)		
	HIROSE ELECTRIC CO., LTD.	CODE NO	CL580-4641-0-05		2/2