










RECOMMENDED PATTERN(5:1)
(RECOMMENDED BOARD THICKNESS t=1.6mm)



PART No.	CODE No.	THE NUMBER OF CONTACT	A	B	C	D	E
DF33C-2P-3.3DSA (24)	CL676-1131-2-24	2	8.4	—	2.5	3.5	6.8
DF33C-3P-3.3DSA (24)	CL676-1132-5-24	3	11.7	6.6	2.5	3.5	6.8
DF33C-4P-3.3DSA (24)	CL676-1133-8-24	4	15.0	9.9	5.1	6.1	10.15
DF33C-5P-3.3DSA (24)	CL676-1134-0-24	5	18.3	13.2	5.1	6.1	10.15
DF33C-6P-3.3DSA (24)	CL676-1135-3-24	6	21.6	16.5	5.1	6.1	10.15

NOTES 1 :IMMERSION DEPTH INTO POTTING SOLUTION:6.5mm
2 :FORCEFULLY UNMATING THE CONNECTORS WILL RISK DAMAGING THEM; THEREFORE,WHEN IT IS DIFFICULT TO UNMATE A CONNECTOR,FIRST GENTLY PRESS DOWN ON IT,THEN RELEASE THE LOCK TO ALLOW REMOVAL.

				3	HIPS	TRAY		
1	 PBT	 WHITE, UL94V-0			2	BRASS	SURFACE: TIN PLATED 1μm min UNDER PLATING: NICKEL PLATED 0.5μm min	
NO.	MATERIAL	FINISH . REMARKS		NO.	MATERIAL	FINISH . REMARKS		
UNITS mm		SCALE 2 : 1	 COUNT 2	DESCRIPTION OF REVISIONS DIS-H-00012938		DESIGNED SS. YAMASAKI	CHECKED SZ. ONO	DATE 20220321
 HIROSE ELECTRIC CO., LTD.		APPROVED : KI. AKIYAMA	20131217	DRAWING NO. EDC3-354785-01				
		CHECKED : HK. UMEHARA	20131217	PART NO. DF33C-*P-3. 3DSA(24)				
		DESIGNED : HT. SATO	20131217	CODE NO. CL676-				
		DRAWN : MI. SAKIMURA	20131217	 				



PART No.	CODE No.	THE NUMBER OF TRAY PACKING
DF33C-2P-3.3DSA(24)	CL676-1131-2-24	135
DF33C-3P-3.3DSA(24)	CL676-1132-5-24	95
DF33C-4P-3.3DSA(24)	CL676-1133-8-24	75
DF33C-5P-3.3DSA(24)	CL676-1134-0-24	60
DF33C-6P-3.3DSA(24)	CL676-1135-3-24	50

NOTES 2 :MINIMUM UNIT OF PURCHASE SHALL BE THE QUANTITY
OF CONNECTORS IN TRAY.

	DRAWING NO. EDC3-354785-01	
	PART NO. DF33C-*P-3.3DSA(24)	
	CODE NO. CL676-	 