





Apr.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD				
RATING	Operating Temperature Range	-55°C to 125°C (Note 1)	Storage Temperature Range	-10°C TO 60°C
	Voltage	50V AC/DC		
	Current	0.3A		
SPECIFICATIONS				
ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
General Examination	Visually and by measuring instrument.	① According to drawing.	X	X
Marking	Confirmed visually.		X	X
ELECTRIC CHARACTERISTICS				
Contact Resistance	20mV AC or less 1kHz,1m A .	① Initial : 80 mΩ MAX. After test : 100 mΩ MAX.	X	—
Insulation Resistance	150V DC.	① 100 MΩ MIN.	X	—
Voltage Proof	150V AC for 1 min.	① No flashover or breakdown.	X	—
MECHANICAL CHARACTERISTICS				
Mechanical Operation	10times insertions and extractions.	① Contact resistance: 100 mΩ MAX. ② No damage, crack or looseness of parts.	X	—
Vibration	Frequency 10 to 500 Hz , Acceleration 49 m/s ² . Sweep time 11min(1 oct/min). 8h for 3 axial directions.	① No electrical discontinuity of 1 μs. ② No damage, crack or Looseness of parts.	X	—
Shock	Acceleration 980 m/s ² duration of pulse 6 ms at 3 times for 3 directions.		X	—
ENVIRONMENTAL CHARACTERISTICS				
Rapid Change of Temperature	Temperature : -55 → +125°C Time : 30 → 30 min Under 1000 cycles. (Relocation time to chanber : within 2-3 min)	① Contact resistance: 100 mΩ MAX.. ② No damage, crack or looseness of parts.	X	—
Dry Heat	Exposed at 125°C±2°C, 1000h. 		X	—
Damp Heat (Steady state)	Exposed at 60±2 °C Relative humidity 90 to 95 %, 1000 h.	① Contact resistance: 100 mΩ MAX. ② Insulation resistance: 50MΩ MIN. ③ No damage, crack or looseness of parts.	X	—
Damp Heat, Cyclic	Exposed at -10 to 65°C, Relative humidity 90 to 96%, 10cycles, total 240h.		X	—
Sulfur Dioxide	Exposed in 25 PPM for 96h, 40°C, 80%. (Refer to JIS C 60068)	① Contact resistance: 100 mΩ MAX.	X	—
Heat resistance of Soldering	Recommended temperature profile soldering area MAX 250°C, 220°C for 60 seconds MAX. Preheating area 150 to 180°C 90 to 120 seconds. Maximum twice action is allowed under the same condition. Recommended manual soldering condition Soldering iron temperature 350°C. Soldering time: wihtin 3 seconds.	① No deformation of case of excessive looseness of the terminals.	X	—
Solderability	Soldering temperature 245±5°C for immersion duration , 3±0.5 seconds.	① A new uniform coating of solder shall cover a minimum of 95% of the surface being immersed.	X	—
COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
 1	DIS-H-00021495	JN MIYAURA	YK. SATAKE	20240930
REMARKS		APPROVED	TY. 001	20221216
Note1: Include the temperature rising by current		CHECKED	RT. SHIMIZU	20221216
Unless otherwise specified, refer to JIS C 5402 and IEC 60512.		DESIGNED	YK. SATAKE	20221215
		DRAWN	JN MIYAURA	20221215
Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.		ELC-401691-51-00
	SPECIFICATION SHEET	PART NO.	BM54B3. 0-40DS-0. 4V (51)	
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL0684-4616-0-51	 1/1