



ELV, RoHS COMPLIANT




RECOMMENDED PCB PATTERN




CONNECTOR MOUNTING SPACE





A (20 : 1)



- NOTE 1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW (REFER TO RIGHT FIG.) USED REFLOW SYSTEM
- NO. OF CYCLES : 1R IN THE AIR OR NITROGEN
 - PEAK : 250°C
 - OVER 230°C : 20~40s
 - PREHEAT : 150~180°C
 - 90~120s
2. TEMPERATURE FOR SOLDERING IRON : 280~300°C WITHIN 2s
3. CO-PLANARITY SHALL BE 0.1mm MAX.
4. RECOMMENDED PCB THICKNESS IS 1.6mm.
5. RECOMMENDED SOLDER THICKNESS IS 0.15mm.



MATED CONNECTORS




2	BRASS	SURFACE PLATING : TIN PLATING 1μm min	5	POLYESTER					
		UNDER PLATING : NICKEL 1μm min	4	POLYSTYRENE					
1	PA	VIOLET	3	BRASS	SURFACE PLATING : TIN PLATING 1μm min				
					UNDER PLATING : NICKEL 1μm min				
NO.	MATERIAL	FINISH	REMARKS	NO.	MATERIAL	FINISH	REMARKS		
UNITS	mm	SCALE	2:1	COUNT	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE
		APPROVED : AH. EDASHIGE 2023. 07. 10 CHECKED : TY. MOGI 2023. 07. 10 DESIGNED : HR. EGAWA 2023. 07. 10 DRAWN : AN. SAIKI 2023. 07. 10		DRAWING NO. EDC-402827-00-00 PART NO. ZE05H-2P-2H(B) CODE NO. CL0752-2145-0-00		1/2			

Apr.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved. In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


Apr.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

PACKING STYLE

PACKING STYLE DRAWING




REEL DIMENSION (FREE)



CARDBOARD DIMENSION (FREE)

W= (405) (mm)
 D= (405) (mm)
 H= (51) (mm)



HRS	DRAWING NO.	EDC-402827-00-00	2/2
	PART NO.	ZE05H-2P-2H (B)	
	CODE NO.	CL0752-2145-0-00	