





May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


ELV, RoHS COMPLIANT



NOTE1. RETAINER ZH05-24DP-R (CL756-2213-0-00) SHOULD BE USED

1. PACKAGING SPECIFICATION


- (1) 250pcs parts are contained in a plastic bag.
- (2) 6 plastic bags are contained in a carton. (Total 1500 pcs in one carton)
- (3) Close the box and seal with packing tape.




2. ASSEMBLY PROCESS

Note: Please refer to the Crimp Quality Standard for details on strip length.

①Strip the cable








②Crimp wire in terminal



NOTE 1: Please use the Hirose crimp tool.


NOTE 2: Please refer to the Crimp Quality Standard to confirm terminal compatibility and check crimp condition.

Continued on the following page


| | | | | | | | | | |
|---|---|-------------------|--|--|---|-----------------------------|------------------|-----------------------|------------------|
| 1 | PA | DARK GRYA UL94V-0 | | | | | | | |
| NO. | MATERIAL | FINISH , REMARKS | | | NO. | MATERIAL | FINISH , REMARKS | | |
| UNITS mm |  | SCALE 2 : 1 | COUNT  1 | DESCRIPTION OF REVISIONS DIS-T-00018145 | | DESIGNED YANG CHUAN XING | | CHECKED MH. SHOUJI | DATE 20230531 |
|  HIROSE ELECTRIC CO., LTD. | | | APPROVED :MH. SHOUJI 20221206 | | DRAWING NO. EDC-395656-00-00 | | | | |
| | | | CHECKED :MH. SHOUJI 20221206 | | PART NO. ZH05-24DP-HU(B) | | | | |
| | | | DESIGNED :YANG CHUAN XING 20221206 | | CODE NO. CL0756-2217-0-00 | | | | |
| | | | DRAWN :YANG CHUAN XING 20221206 | |  1  4 | | | | |

May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


- ③Insert contact and push until a click is heard.
※Please take care to ensure that the terminal is inserted in the correct orientation.




- NOTE 1: Holding the cable, please insert straight into the housing.
Do not use more than 10N of force during this process.
- NOTE 2: If the crimped terminal does not enter the housing smoothly the first time, remove it and then re-insert.
- ※Please hold the cable as below picture and insert it with a force less than 10 N, or terminal will be deformed. Please use a new terminal in this case.




- ④After insertion, confirm that the terminal has been inserted correctly by pulling the cable lightly, the pulling force must be less than 10N.




- ⑤Press retainer into housing until it clicks in the direction of the arrow.




After setting the retainer, please inspect the housing head-on to confirm that the retainer is not protruding in any way.



Confirm the retainer is visible.




Connector Cross-Section



* Correct retainer is used

OK

Connector Cross-Section



* Retainer part number is wrong

NOT OK


HRS

| | |
|-------------|------------------|
| DRAWING NO. | EDC-395656-00-00 |
| PART NO. | ZH05-24DP-HU(B) |
| CODE NO. | CL0756-2217-0-00 |



May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

3. REPAIR PROCESS


- ①Insert the special tool in direction ① and push down the lance,
and remove the retainer from direction ②.
Note: Please refer to the following section for details on the special tool.




Connector Cross-Section



Connector Cross-Section




- ②Insert the special tool into the terminal cavity and push to the end
with the tool flat side up as below picture.
Maintain this position and pull the applicable cable carefully to remove the terminal.
Note: Please refer to the following section for details on the special tool.




*Recommend to operate under proper illumintion to enhance workability

Condition at inserted repair tool



Note: Housing is not reusable. Please use new parts after repairing.

Note: In case the terminal lance and/or retainer lance has been deformed, please use new parts.



HRS

| | |
|-------------|------------------|
| DRAWING NO. | EDC-395656-00-00 |
| PART NO. | ZH05-24DP-HU(B) |
| CODE NO. | CL0756-2217-0-00 |

3/4

May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

4. Other / Notes

- 1) Do not touch the terminal contact points or the interior of the barrel.
- 2) In the event that the terminal must be handled, please wear gloves in order to prevent corrosion.
- 3) Placing items on top of a terminal or dropping a terminal may result in shape deformities or contamination. Please handle terminals with care.
- 4) In the event of terminals becoming tangled, please do not forcibly pull or bend them apart, but disentangle them carefully.
- 5) Use caution when handling terminals so as to avoid deformation.
- 6) Make sure that the terminals of crimped cables do not become entangled.
When bundling or stacking cables, please prevent the terminals from being subjected to any external force.
- 7) Use caution to ensure that the part is not subjected to any large impacts.
- 8) Avoid storing in dusty areas.
- 9) Do not place wire harnesses on the floor.
- 10) Refrain from any handling that may result in terminal damage or deformation.
- 11) Do not use if the housing is dropped.

Repair tool summary

Retainer repair tools - Part Number Summary

| Applicable Part | Repair Tool Name | Repair Tool Part Number |
|------------------|------------------|-------------------------|
| ZH05-##DP-HU(##) | ZH05/R/RE-MD | 902-5162-0 |

(##) =specification number

Crimp Terminal crimping tool - Part Number Summary

| Applicable Part | Connection Tool Name | | Connection Tool Part Number |
|------------------|----------------------|------------------|-----------------------------|
| ZH05-2224PCF(##) | applicator | AP105-ZH05-2224P | 901-5253-0 |

(##) =specification number

Crimp Terminal repair Tool - Part Number Summary

| Applicable Part | Repair Tool Name | Repair Tool Part Number |
|------------------|------------------|-------------------------|
| ZH05-2224PCF(##) | ZH05/RE-MD | 902-5161-0 |

(##) =specification number

5. CRIMP QUALITY STANDARD


1. Scope

This technical specification prescribes crimp condition of ZH05-2224PCF (CL756-2001-0)

2. Applicable wire

- Applicable wire size : 0.22~0.35SQ
- Applicable insulation size : $\phi 0.9 \sim \phi 1.4$

3. Quality standard



| CHECK POINT | | MEASURE (mm) | |
|--|-------------------|--------------|-----------|
| COVER LOCATION | | A | 0.3~0.8 |
| LOCATION OF TIP OF THE CORE | | B | 0.1~0.6 |
| BELL-MOUTH | C1 | | 0.1~0.4 |
| | C2 | | 0.1 max |
| | C3 | | 0.15 max |
| BEND-UP | D | | 2° max |
| BEND-DOWN | E | | 3° max |
| TWIST | F | | ±2° max |
| ROLLING | G | | ±5° max |
| STRIP LENGTH | H | | 4.0~4.6 |
| WIDTH | WIRE BARREL | I | 1.36 max |
| | INSULATION BARREL | J | 1.47 max |
| HEIGHT OF METAL CUT-OUT TEETH | K | | 0.15 max |
| CUT-OFF TAB | L | | 0.1 max |
| DIFFERENCE IN LEVEL ON TRANSITION PART APPLY ONLY BEND-UP | M | | 0.2 max |
| DIFFERENCE IN LEVEL BETWEEN WIRE BARREL AND INSULATION BARREL | Q | | 0.2~0.25 |
| DISTANCE BETWEEN WIRE-CRIMPER AND WIRE-ANVIL | R | | 0.15~0.31 |

Note1. Refer to a crimp condition list for the crimp height.

Note2. A barrel may nip at insulation after crimping, but there is no problem in product function.

Note3. Please confirm that the terminal which did crimp enters a housing.

HRS

| | |
|-------------|------------------|
| DRAWING NO. | EDC-395656-00-00 |
| PART NO. | ZH05-24DP-HU(B) |
| CODE NO. | CL0756-2217-0-00 |

3/4