







Jun.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


ELV, RoHS COMPLIANT




CONNECTOR MOUNTING SPACE



MATED CONNECTORS




- NOTE 1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW (REFER TO RIGHT FIG.)
USED REFLOW SYSTEM : IR IN THE AIR OR NITROGEN
NO. OF CYCLES : 2 MAX
PEAK : 250°C
OVER 230°C : 20~40s
PREHEAT : 150~180°C 90~120s
2. TEMPERATURE FOR SOLDERING IRON : 280~300°C WITHIN 2s
3. CO-PLANARITY SHALL BE 0.1mm MAX.
4. RECOMMENDED PCB THICKNESS IS 1.6mm.
5. RECOMMENDED SOLDER THICKNESS IS 0.15mm.




3	BRASS	SURFACE PLATING : TIN PLATING 1μm min			
		UNDER PLATING : NICKEL 1μm min	6	POLYESTER	
2	BRASS	SURFACE PLATING : TIN PLATING 1μm min	5	POLYSTYRENE	
		UNDER PLATING : NICKEL 1μm min	4	BRASS	SURFACE PLATING : TIN PLATING 1μm min
1	PA	GRAY UL94V-0			UNDER PLATING : NICKEL 1μm min
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED CHECKED DATE
HIROSE ELECTRIC CO., LTD.		APPROVED : HK. UMEHARA	20190323	DRAWING NO.	EDC-383548-00-00
		CHECKED : HK. UMEHARA	20190323	PART NO.	ZE05-20DP-2H(A)
		DESIGNED : YH. MAMADA	20190323	CODE NO.	CL752-2119-0-00
		DRAWN : DS. HIROWATARI	20190323		


PACKING STYLE DRAWING



REEL DIMENSION (FREE)



CARDBOARD DIMENSION (FREE)



W=(405) (mm)
D=(405) (mm)
H= (63) (mm)