







May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



ELV. RoHS COMPLIANT



EMBOSS PACKING SPECIFICATIONS(FREE)

1. PLACE CONNECTORS INTO EMBOSSED CARRIER TAPE.


← DIRECTION OF UNREELING




300 PCS/REEL


2. PUT A REEL INTO CARTON BOX

W = (405) (mm)
D = (405) (mm)
H = (51) (mm)



- NOTE1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW(REFER TO RIGHT FIG.)
REFLOW HEATING METHODS : FAR-INFLARED, IN THE AIR OR NITROGEN.
REFLOW No. : MAX 2TIMES
PEAK TEMPERATURE : 250℃
ABOVE 230℃ : 20~40s
PREHEAT : 150~180℃(60~120s)
2. SOLDERING TEMPERATURE : 280~300℃, MAX2s
3. COPLANARITY OF LEADS SHALL BE UNDER 0.1mm.
4. RECOMMENDED THICKNESS FOR PC BOARD IS 1.6mm.
5. RECOMMENDED THICKNESS FOR SOLDER PASTE IS 0.15mm.



2	BRASS	TIN PLATING		4	BRASS	TIN PLATING				
1	PPS	BLACK		3	BRASS	TIN PLATING				
NO.	MATERIAL	FINISH , REMARKS		NO.	MATERIAL	FINISH , REMARKS				
UNITS mm		SCALE 2 : 1		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE		
				APPROVED : HH. TSUKUMO 20200321				DRAWING NO. EDC-167884-55-00		
				CHECKED : HH. TSUKUMO 20200321				PART NO. GT8E-12DP-2H(55)		
				DESIGNED : DONGCHAN KIM 20200221				CODE NO. CL758-1008-2-55		
 HIROSE ELECTRIC CO., LTD.		DRAWN : YK. MITSUISHI 20200220		 1						