







May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

RoHS, ELV COMPLIANT


NOTES

- 1) SMT COPLANARITY: 0.1mm MAX.
- 2) RECOMMENDED THICKNESS OF SOLDERING PASTE: 0.12mm
- 3) RECOMMENDED REFLOW PROFILE (SEE RIGHT GRAPH)
TYPE:IR REFLOW
ATMOSPHERE: AIR OR N₂
CYCLE TIME: UP TO 2 CYCLES OF REFLOW SOLDERING ARE POSSIBLE UNDER THE CONDITIONS, PROVIDED THAT THERE IS A RETURN TO NORMAL TEMPERATURE BETWEEN THE FIRST AND SECOND CYCLE.
PEAK TEMPERATURE: 250°C
230°C MIN. FOR 20 TO 40 SECONDS.
PREHEATING AREA 150°C TO 180°C FOR 60 TO 120 SECONDS.
- 4) HAND SOLDERING: 280-300°C, 2S MAX.
- 5) RECOMMENDED THICKNESS OF PCB: 1.6mm
- 6) FOR THE PREVENTION EXCESSIVE STRESS FOR CONNECTOR AND PCB, WE RECOMMEND ADDITIONAL SUPPORT MECHANISM IF THE FLANGE WAS ELIMINATED.
- 7) THIS PRODUCT CAN REPLACE CL767-0176-2-30 GT17HN-4DP-2H(C)<30>.



2	PA	BLUE		4	BRASS	TIN PLATING				
1	COPPER ALLOY	TIN PLATING		3	BRASS	TIN PLATING				
NO.	MATERIAL	FINISH , REMARKS		NO.	MATERIAL	FINISH , REMARKS				
UNITS mm				SCALE 2 : 1		COUNT 1	DESCRIPTION OF REVISIONS DIS-T-00006678	DESIGNED TS. KUBOTA	CHECKED EJ. WAKATSUKI	DATE 20200909
 HIROSE ELECTRIC CO., LTD.				APPROVED : KI. HIROKAWA		20200416		DRAWING NO. EDC-169398-58-00		
				CHECKED : EJ. WAKATSUKI		20200415		PART NO. GT17HN2-4DP-2H(C)(58)		
				DESIGNED : TS. KUBOTA		20200325		CODE NO. CL767-0295-1-58		
				DRAWN : YK. MITSUISHI		20200324		 		

May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



HRS	DRAWING NO.	EDC-169398-58-00		
	PART NO.	GT17HN2-4DP-2H(C)(C58)		
	CODE NO.	CL767-0295-1-58		
				2/2