



Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

ELV, RoHS COMPLIANT




RECOMMENDED PCB PATTERN



Additional of [TRAY PACKING SPECIFICATION]

TRAY PACKING SPECIFICATION
10 TRAYS STACKING.
ODD NUMBER TRAYS AND EVEN NUMBER TRAYS ARE REVERSE DIRECTION.
TOP TRAY IS EMPTY.



NOTE 1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW
(REFER TO RIGHT FIG.)
USED REFLOW SYSTEM


: IR IN THE AIR OR NITROGEN
NO. OF CYCLES : 2 MAX
PEAK : 250°C
OVER 230°C : 20~40s
PREHEAT : 150~180°C
60~120s

2. TEMPERATURE FOR SOLDERING IRON
: 280~300°C WITHIN 2s

3. CO-PLANARITY SHALL BE 0.1mm MAX.

4. RECOMMENDED PCB THICKNESS IS 1.6mm.

5. RECOMMENDED SOLDER THICKNESS IS 0.15mm.



2	BRASS	TIN PLATED T=0.64	4	BRASS	TIN PLATED T=0.4
1	PPS	BLACK	3	BRASS	TIN PLATED T=0.64
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT 1	DESCRIPTION OF REVISIONS DIS-T-00006321	DESIGNED DONGCHAN KIM
		APPROVED : AR. SHIRAI	20160914	DRAWING NO.	EDC-360213-00-00
		CHECKED : HS. OZAWA	20160914	PART NO.	GT25H2-24DP-2.2V
		DESIGNED : TK. SHISHIKURA	20160914	CODE NO.	CL775-0083-8-00
		DRAWN : TK. SHISHIKURA	20160914		
		DATE	20200703		