



Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

ELV. RoHS COMPLIANT










PIN ASSIGNMENT
6 12 5 11 4 10 3 9 2 8 1 7




RECOMMENDED PCB PATTERN

HRS DRAWING FOR REFERENCE

NOTE1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW
(REFER TO RIGHT FIG.)
USED REFLOW SYSTEM
: IR IN THE AIR OR NITROGEN
NO. OF CYCLES : 2 MAX
PEAK : 250℃
OVER 230℃ : 20~40s
PREHEAT : 150~180℃
60~120s

2. TEMPERATURE FOR SOLDERING IRON
:280~300℃ WITHIN 2s
3. LEAD CO-PLANARITY SHALL BE 0.1mm MAX.
4. RECOMMENDED PCB THICKNESS IS 1.6mm
5. RECOMMENDED SOLDER THICKNESS IS 0.15mm.



NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
3	BRASS	TIN PLATED	6	PET	
2	BRASS	TIN PLATED	5	PS	
1	PA	BLACK	4	BRASS	TIN PLATED


UNITS	SCALE		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	2 : 1	△2	1	DIS-T-00006626	DONGCHAN KIM	HH. TSUKUMO	20200902

HIROSE ELECTRIC CO., LTD.


APPROVED	AR. SHIRAI	20180622	DRAWING NO. EDC-361744-10-00
CHECKED	HS. OZAWA	20180622	PART NO. GT25H2-12DP-2.2H(10)
DESIGNED	YT. HAYAKAWA	20180622	
DRAWN	GYEONGMIN LEE	20180622	CODE NO. CL775-0092-9-10 △2 1/2

Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

PACKAGING SPECIFICATION




② REEL DIMENSION (FREE)



HRS DRAWING FOR REFERENCE

CARDBOARD DIMENSION (FREE)



BOX SIZE
W=(405)(mm)
D=(405)(mm)
H=(51) (mm)

1 REEL / BOX

HRS	DRAWING NO.	EDC-361744-10-00
	PART NO.	GT25H2-12DP-2.2H(10)
	CODE NO.	CL775-0092-9-10 ② 2/2

FORM HC0011-5-8