

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	△ ₂ -55℃ TO 85℃(NOTE 1)	STORAGE TEMPERATURE RANGE	-10℃ TO 60℃	
	VOLTAGE	△ ₂ 50V AC/DC	APPLICABLE CONNECTOR	BM28B0. 6-10DP/2-0. 35V	
	CURRENT	SIGNAL CONTACT : 0. 3A POWER CONTACT : 5. 0A			
SPECIFICATIONS					
ITEM		TEST METHOD		REQUIREMENTS	QT AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X X
MARKING		CONFIRMED VISUALLY.			X X
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE		20mV AC OR LESS 1kHz,1m A .		Signal contact resistance: 70 m Ω MAX. △ ₂ Power contact resistance: 15 m Ω MAX.	X -
INSULATION RESISTANCE		100V DC.		50MΩ MIN.	X -
VOLTAGE PROOF		150V AC FOR 1 min. △ ₂		NO FLASHOVER OR BREAKDOWN.	X -
MECHANICAL CHARACTERISTICS					
MECHANICAL OPERATION		10TIMES INSERTIONS AND EXTRACTIONS.		① Signal contact resistance: 70 m Ω MAX. △ ₂ Power contact resistance: 15 m Ω MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X -
VIBRATION		FREQUENCY 10 TO 55 TO 10 Hz,APPROX 5min, SINGLE AMPLITUDE 0.75 mm,10CYCLES, FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X -
SHOCK		490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X -
ENVIRONMENTAL CHARACTERISTICS					
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55 → +85℃ TIME 30 → 30 min UNDER 5 CYCLES. (RELOCATION TIME TO CHANBER : WITHIN 2-3 min)		① Signal contact resistance: 70 m Ω MAX. △ ₂ Power contact resistance: 15 m Ω MAX. ② INSULATION RESISTANCE: 50MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X -
DAMP HEAT (STEADY STATE)		EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.		① Signal contact resistance: 70 m Ω MAX. △ ₂ Power contact resistance: 15 m Ω MAX. ② INSULATION RESISTANCE: 25MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X -
SULPHUR DIOXIDE		EXPOSED IN 25 PPM FOR 96h,25℃,75%. (REFER TO JIS C 60068)		① Signal contact resistance: 70 m Ω MAX. △ ₂ Power contact resistance: 15 m Ω MAX.	X -
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△ ₂	8	DIS-H-00019757	ST. HIRONAKA	RT. SHIMIZU	20240125
REMARKS			APPROVED	MO. ISHIDA	20150715
NOTE1: INCLUDE THE TEMPERATURE RISING BY CURRENT			CHECKED	TS. MIYAZAKI	20150714
Unless otherwise specified, refer to JIS C 5402 and IEC 60512.			DESIGNED	YK. SATAKE	20150714
			DRAWN	KR. AJITO	20150714
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-365298-51-01
HRS	SPECIFICATION SHEET		PART NO.	BM28B0. 6-10DS/2-0. 35V (51)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL0673-5044-0-51	△ ₂ 1/1