

Jun.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD						
RATING	OPERATING TEMPERATURE RANGE	-55°C TO + 105°C (NOTE 1)		STORAGE TEMPERATURE RANGE	-10°C TO + 60°C (NOTE 3)	
	OPERATING HUMIDITY RANGE	20% TO 80% (NOTE 2)		STORAGE HUMIDITY RANGE	40% TO 70% (NOTE 3)	
	CURRENT (*1)	AWG8	42A	APPLICABLE CONTACT	DF60-8SC (F) A (##)	
		AWG10	34A		DF60-1012SC (F) A	
AWG12		28A	VOLTAGE	1000V AC/DC		
	Rated voltage	Rated current		Overvoltage category	IP- degree	
UL	600V AC/DC	AWG8:55A/AWG10:50A/AWG12:40A (AT AMBIENT TEMP. 25°C) (NOTE 5)		—	—	
C-UL	600V AC/DC	See above(*1) (Temp. rise up 30°C MAX)		—	—	
TÜV	600V AC/DC	See above(*1)		III	IP20 (Note 7)	
SPECIFICATIONS						
ITEM	TEST METHOD		REQUIREMENTS	QT	AT	
CONSTRUCTION						
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X	X	
MARKING	CONFIRMED VISUALLY.			X	X	
ELECTRIC CHARACTERISTICS						
INSULATION RESISTANCE	1000V DC.		1000MΩ MIN.	X	—	
VOLTAGE PROOF	3000V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	X	—	
MECHANICAL CHARACTERISTICS						
VIBRATION	FREQUENCY 10 TO 500 Hz, TOTAL AMPLITUDE 1.5 mm, Acceleration of 98 m/s ² , AT 2 h, FOR 3 DIRECTIONS.		NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—	
SHOCK	490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.		NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—	
Contact extraction force	Pull out the cable after housing fixation.		49N MIN	X	—	
ENVIRONMENTAL CHARACTERISTICS						
DAMP HEAT (STEADY STATE)	EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.		① INSULATION RESISTANCE: 1000MΩ MIN. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—	
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55°C → +105°C TIME 30min → 30min UNDER 25 CYCLES. (THE TRANSFERRING TIME OF THE TANK IS 2-3 min) (AFTER LEAVING THE ROOM TEMPERATURE FOR 1-2h.)		① INSULATION RESISTANCE: 1000MΩ MIN. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—	
DRY HEAT	EXPOSED AT 105 ± 2°C, 250h (AFTER LEAVING THE ROOM TEMPERATURE FOR 1-2h.)		① INSULATION RESISTANCE: 1000MΩ MIN. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—	
Cold	Exposed at -55±3°C, 96h		① Contact resistance: 2mΩ MAX. ② Insulation resistance: 1000MΩ MIN. ③ No damage, crack or looseness of parts	X	—	
Remarks Note 1: Include the temperature rising by current. Note 2: No condensing Note 3: Apply to the condition of long term storage for unused products before mount on pcb, After mounted on pcb, operating temperature and humidity range is applied for interim storage during transportation.						
△	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
Unless otherwise specified, refer to IEC 60512.			APPROVED	HS. OKAWA	18.03.16	
			CHECKED	ST. WADA	18.03.16	
			DESIGNED	TT. OHSAKO	18.03.13	
			DRAWN	TT. OHSAKO	18.03.13	
Note QT: Qualification Test AT: Assurance Test X: Applicable Test			DRAWING NO.		ELC-379271-00-00	
HRS	SPECIFICATION SHEET		PART NO.	DF60F-3S-10.16C		
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL680-4002-0-00	△ 1/2	

(Note 4) Derating curve takes manufacturing tolerances into consideration as well as uncertainties in temperature measurement and the measuring set up and is derived from the basic curve multiplied by 0.8 calculation.

(Note 5) The value of rated current differs depending on the ambient temperature. It is recommended to use the product within the derating curve zone.


(Note 6) Measurement method of derating curve is shown below.

- Test specimen: Unused DF60-6P-10.16DS(27).
Unused DF60-6S-10.16C
Unused DF60-8SCFA
- Test cable spec: AWG 8
- Test condition: Turn on electricity under the static state and measure.
(Test report # TR680E-20802)


(Note 7) Refer to "ETAD-H0653-00".

[Reference]

Derating curve



Temperature rise curve



Note QT:Qualification Test AT:Assurance Test X:Applicable Test

Drawing no.

ELC-379271-00-00



Specification sheet

Part no.

DF60F-3S-10.16C

Hirose electric co., ltd.

Code no.

CL680-4002-0-00



2/2