




### STYLE AND DIMENSION OF REEL(FREE SIZE)



| 製品名                        | H  | J    | K    | L    | M    | N    |
|----------------------------|----|------|------|------|------|------|
| DF40HC(3.5)-200S-0.4V(51)  | 16 | —    | 7.5  | 6.9  | 21.5 | 17.5 |
| DF40HC(3.5)-240S-0.4V(51)  | 16 | —    | 7.5  | 7.7  | 21.5 | 17.5 |
| DF40HC(3.5)-300S-0.4V(51)  | 24 | —    | 11.5 | 8.9  | 29.5 | 25.5 |
| DF40HC(3.5)-400S-0.4V(51)  | 24 | —    | 11.5 | 10.9 | 29.5 | 25.5 |
| DF40HC(3.5)-440S-0.4V(51)  | 24 | —    | 11.5 | 11.7 | 29.5 | 25.5 |
| DF40HC(3.5)-500S-0.4V(51)  | 24 | —    | 11.5 | 12.9 | 29.5 | 25.5 |
| DF40HC(3.5)-600S-0.4V(51)  | 24 | —    | 11.5 | 14.9 | 29.5 | 25.5 |
| DF40HC(3.5)-700S-0.4V(51)  | 32 | 28.4 | 14.2 | 16.9 | 37.5 | 33.5 |
| DF40HC(3.5)-800S-0.4V(51)  | 32 | 28.4 | 14.2 | 18.9 | 37.5 | 33.5 |
| DF40HC(3.5)-900S-0.4V(51)  | 44 | 40.4 | 20.2 | 20.9 | 49.5 | 45.5 |
| DF40HC(3.5)-1000S-0.4V(51) | 44 | 40.4 | 20.2 | 22.9 | 49.5 | 45.5 |

HRS

|                |                           |                                                                                       |                                                                                       |
|----------------|---------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| DRAWING<br>NO. | EDC3-318048-01            |                                                                                       |                                                                                       |
| PART<br>NO.    | DF40HC(3.5) -*DS-0.4V(51) |                                                                                       |                                                                                       |
| CODE<br>NO.    | CL684                     |  |  |