

Feb.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO +125 °C	STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C ⁽¹⁾	
	VOLTAGE	\triangle 60 V AC/DC	STORAGE HUMIDITY RANGE	RELATIVE HUMIDITY 85% MAX	
	CURRENT	2 A		(NOT DEWED)	
SPECIFICATIONS					
ITEM	TEST METHOD	REQUIREMENTS	QT	AT	
CONSTRUCTION					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	x	x	
MARKING	CONFIRMED VISUALLY.		x	x	
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE	1A DC.	10 m Ω MAX.	x	-	
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD	10 mV AC MAX, 0.1 mA(DC OR 1000Hz)	10 m Ω MAX.	x	-	
MECHANICAL CHARACTERISTICS					
MECHANICAL OPERATION	30 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 20 m Ω MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-	
VIBRATION	FREQUENCY 20 TO 200Hz (88m/s ²) SWEEP TIME 3min.(ROUND TRIP) AT 3h FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 7 Ω MIN, 1 μ s MIN. ② CONTACT RESISTANCE: 20 m Ω MAX. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-	
SHOCK	981m/s ² DURATION OF PULSE 6ms AT 3 TIMES FOR 6 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 7 Ω MIN, 1 μ s MIN. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-	
ENVIRONMENTAL CHARACTERISTICS					
DAMP HEAT (STEADY STATE)	EXPOSED AT 60 °C, 90 ~ 95 %, 96 h.	① CONTACT RESISTANCE: 20 m Ω MAX. ② INSULATION RESISTANCE:100 M Ω MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-	
RAPID CHANGE OF TEMPERATURE	TEMPERATURE- 40 →ROOM TEMP →125°C→ ROOM TEMP TIME 30 → 5 → 30 → 5 min UNDER 1000 CYCLES.	① CONTACT RESISTANCE: 20 m Ω MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-	
DRY HEAT	EXPOSED AT 140°C, 120 h.	① CONTACT RESISTANCE: 20 m Ω MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-	
COLD	EXPOSED AT -40°C , 120 h.	① CONTACT RESISTANCE: 20 m Ω MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	-	
RESISTANCE TO SO ₂ GAS	EXPOSED IN 25 PPM AT 75% MIN FOR 96h.	① CONTACT RESISTANCE: 20 m Ω MAX.	x	-	
COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
\triangle 3 1	DIS-T-00006017	YH. MAMADA	HH. TSUKUMO	20200403	
REMARK (NOTE1) "STORAGE" means a long-term storage state for the unused product before assembly to PCB.		APPROVED	HK. UMEHARA	20170411	
		CHECKED	HK. UMEHARA	20170411	
		DESIGNED	KT. MATSUDA	20170411	
		DRAWN	KT. MATSUDA	20170411	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.	ELC-368625-00-00		
HRS	SPECIFICATION SHEET	PART NO.	ZE05-2022SCF		
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL752-2001-0-00	\triangle 3	1/1