




-
- Figure 1 is a line graph showing the temperature profile of the furnace. The vertical axis is labeled "TEMP. (°C)" and ranges from 100 to 250 in increments of 50. The horizontal axis is labeled "TIME (s)". The profile starts at 180°C, rises to 150°C, then to 230°C, peaks at 250°C, and finally drops to 100°C. Time intervals are marked: 90 ± 30s for the first rise, 30 ± 10s for the second rise, and 30 ± 10s for the cooling phase.



RECOMMENDED PANNEL LAYOUT



RECOMMENDED PCB LAYOUT


$$A(4:1)$$

2	PPS	GREEN	5	PS	NATURAL			
1	COPPER ALLOY	TIN PLATING	4	BRASS	TIN PLATING			
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS			
UNITS mm		SCALE 2 : 1		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
 HIROSE ELECTRIC CO., LTD.		APPROVED : KI. HIROKAWA		20200326	DRAWING NO. EDC-167010-56-00			
		CHECKED : E.J. WAKATSUKI		20200325	PART NO. GT17HN-4DP-2HCB) (56)			
		DESIGNED : TS. KUBOTA		20200325	CODE NO. CL767-0175-0-56			
		DRAWN : YK. MITSUISHI		20200221	 1/2			

May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

