




-
- Figure 1 is a line graph showing the temperature profile of the furnace. The vertical axis is labeled 'TEMP. (°C)' and ranges from 100 to 250 in increments of 50. The horizontal axis is labeled 'TIME (s)'. The profile starts at 180°C, rises to 150°C, then to 230°C, and finally to a peak of 250°C. The time intervals are marked as 90 ± 30s, 30 ± 10s, and 30 ± 10s.



RECOMMENDED PANNEL LAYOUT




RECOMMENDED PCB LAYOUT



				5	PS	NATURAL			
2	PPS	BLUE		4	BRASS	TIN PLATING			
1	COPPER ALLOY	TIN PLATING		3	BRASS	TIN PLATING			
NO.	MATERIAL	FINISH . REMARKS		NO.	MATERIAL	FINISH . REMARKS			
UNITS mm		SCALE 2 : 1		COUNT 1	DESCRIPTION OF REVISIONS DIS-T-00006678		DESIGNED TS. KUBOTA	CHECKED EJ. WAKATSUKI	DATE 20200909
 HIROSE ELECTRIC CO., LTD.		APPROVED : KI. HIROKAWA			20200331		DRAWING NO. EDC-167011-66-00		
		CHECKED : EJ. WAKATSUKI			20200330		PART NO. GT17HN-4DP-2H(C)(C)(66)		
		DESIGNED : TS. KUBOTA			20200325		CODE NO. CL767-0176-2-66		
		DRAWN : YK. MITSUSHI			20200317		 		

May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



HRS

DRAWING NO.	EDC-167011-66-00
PART NO.	GT17HN-4DP-2H(C)(66)
CODE NO.	CL767-0176-2-66

1/2